

Quick coupling EAMD-67-51-20-32X32-U

Part number: 3717812

FESTO



Data sheet

Feature	Value
Diameter of holder 1	20 mm
Diameter of holder 2	32 mm
Size	67
Nominal length	51 mm
Type code	EAMD
Mounting position	Any
Max. rotational speed	4500 1/min
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	374 kgmm ²
Transferable torque	120 Nm
Product weight	744 g
Note on materials	RoHS-compliant