

# Adaptive gripper finger DHAS-GF-120-U-BU

Part number: 3998959

FESTO



## Data sheet

| Feature                          | Value                                     |
|----------------------------------|-------------------------------------------|
| Size                             | 120                                       |
| Type code                        | DHAS                                      |
| Mounting position                | Any                                       |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress             |
| For use in the food industry     | See supplementary material information    |
| Ambient temperature              | 10 °C ... 50 °C                           |
| Product weight                   | 29 g                                      |
| Note on materials                | Free of copper and PTFE<br>RoHS-compliant |
| Clamping jaws material           | TPE-U(PU)                                 |