

# Position indicator SASF-S2-B-F-A56

Part number: 4077125

FESTO



## Data sheet

Feature	Value
Adjustment range of swivel angle	0 deg ... 90 deg
Type code	SASF
Dimensions W x L x H	Ø 115 x 62
Vibration resistance	Transport application test with severity level 2 as per FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27
Ambient temperature	-25 °C ... 70 °C
Product weight	140 g
Type of mounting	as per VDI/VDE 3845
Housing colour	Black
Note on materials	Contains paint-wetting impairment substances RoHS-compliant
Spacer element material	PA
Housing material	PA PP High-alloy stainless steel
Material of screws	High-alloy stainless steel