

Quick connector ACK-1/2-PK-13

Part number: 4099

FESTO



Data sheet

| Feature | Value |
|--|--|
| Nominal width | 12 mm |
| Type code | ACK |
| Type of seal on screwed trunnion | Sealing ring |
| Mounting position | Any |
| Maritime classification | See certificate |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:-:-] Water as per manufacturer's declaration at www.festo.com |
| Information on operating and pilot media | Operation with oil lubrication possible |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| Ambient temperature | -10 °C ... 60 °C |
| Pneumatic connection 1 | Internal thread G1/2 |
| Pneumatic connection 2 | for pneumatic tubing inside diameter 13 mm |
| Note on materials | RoHS-compliant |
| Housing material | Aluminum |