

# Axial kit EAMM-A-V25-40P

Part number: 4491059

FESTO



## Data sheet

| Feature                  | Value                  |
|--------------------------|------------------------|
| Nominal length           | 41 mm                  |
| Type code                | EAMM-A                 |
| Mounting position        | Any                    |
| Max. rotational speed    | 10000 1/min            |
| Storage temperature      | -25 °C ... 60 °C       |
| Relative air humidity    | 0 - 95 %               |
| Degree of protection     | IP40                   |
| Ambient temperature      | -10 °C ... 60 °C       |
| Mass moment of inertia   | 0.19 kgmm <sup>2</sup> |
| Transferable torque      | 0.5 Nm                 |
| Product weight           | 90 g                   |
| Interface code, actuator | V25                    |
| Interface code, motor in | 40P                    |
| Note on materials        | RoHS-compliant         |