

Axial kit EAMM-A-V20-28A

Part number: 4505258

FESTO



Data sheet

| Feature | Value |
|--------------------------|-------------------------|
| Nominal length | 36.4 mm |
| Type code | EAMM-A |
| Mounting position | Any |
| Max. rotational speed | 10000 1/min |
| Storage temperature | -25 °C ... 60 °C |
| Relative air humidity | 0 - 95 % |
| Degree of protection | IP40 |
| Ambient temperature | -10 °C ... 60 °C |
| Mass moment of inertia | 0.022 kgmm ² |
| Transferable torque | 0.2 Nm |
| Product weight | 27 g |
| Interface code, actuator | V20 |
| Interface code, motor in | 28A |
| Note on materials | RoHS-compliant |