

Memory card CAMC-M-MS-G32

Part number: 4553880

FESTO



Data sheet

Feature	Value
Ambient temperature	-25 °C ... 85 °C
Note on materials	RoHS-compliant
Type code	CAMC
Storage capacity	3.2E10 byte
Application note	The device was developed, designed and built exclusively for industrial and commercial applications. The device has not been approved for private use.
Design	microSDHC
Structural design	MLC
Speed class	Class 10
Max. read speed	20 MB/s
Max. write speed	20 MB/s
Number of write/delete cycles	64 TBW