

# Ball valve VZBE-11/4-T-63-D-2-M-V15V15

Part number: 4745220

FESTO



## Data sheet

Feature	Value
Type code	VZBE
Structural design	2-way ball valve with hand lever
Actuation type	Mechanical
Sealing principle	Soft
Mounting position	Any
Type of mounting	Line installation
Fitting connection	1 1/4 NPT
Switching position indication	Slot direction = flow direction
Inside diameter	32 mm
Nominal width DN	32
Valve function	2/2
Flow direction	Reversible
Nominal pressure of fitting PN	63

Feature	Value
Breakaway torque at differential pressure, nominal pressure, fitting PN	15 Nm
Based on norm	ASME B1.20.1
Symbol	00991458
Medium	Vapor Compressed air as per ISO 8573-1:2010 [:-:-] Inert gas Water Neutral liquids
Temperature of medium	-20 °C ... 200 °C
Flow rate Kv	160 m <sup>3</sup> /h
Note on materials	Contains paint-wetting impairment substances RoHS-compliant
Housing material	Cast stainless steel
Material number of housing	1.4408
Seat seal material	PTFE
Seals material	PTFE
Ball material	Cast stainless steel
Material number for ball	1.4408
Shaft material	High-alloy stainless steel
Material number for shaft	1.4401
Product weight	1100 g
Certification	CRN
CE marking (see declaration of conformity)	as per EU pressure equipment directive
Explosion prevention and protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Corrosion resistance class (CRC)	3 - High corrosion stress