

Parallel kit EAMM-U-45-V25-40P-63

Part number: 4782056

FESTO



Data sheet

Feature	Value
Size	45
Center-to-center distance	63 mm
Type code	EAMM-U
Mounting position	Any
Gear ratio	1:1
Max. rotational speed	3600 1/min
Storage temperature	-20 °C ... 60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	0 °C ... 50 °C
Mass moment of inertia	4.35 kgmm ²
No-load driving torque	0.05 Nm
Transferable torque	0.5 Nm
Product weight	253 g
Interface code, actuator	V25
Interface code, motor in	40P
Note on materials	RoHS-compliant