

Ball valve
VZBE-3/4-T-63-T-2-F0304-V15V15
Part number: 4809118

FESTO



Data sheet

Feature	Value
Type code	VZBE
Structural design	2-way ball valve
Actuation type	Mechanical
Sealing principle	Soft
Mounting position	Any
Type of mounting	Line installation
Fitting connection	3/4 NPT
Switching position indication	Slot direction = flow direction
Flange hole pattern	F0304
Inside diameter	20 mm
Nominal width DN	20
Valve function	2/2
Flow direction	Reversible

Feature	Value
Nominal pressure of fitting PN	63
Breakaway torque at differential pressure, nominal pressure, fitting PN	9 Nm
Based on norm	ASME B1.20.1 ISO 5211
Symbol	00991458
Medium	Vapor Compressed air as per ISO 8573-1:2010 [:-:-] Inert gas Water Neutral liquids
Temperature of medium	-20 °C ... 200 °C
Flow rate Kv	59 m³/h
Note on materials	Contains paint-wetting impairment substances RoHS-compliant
Housing material	Cast stainless steel
Material number of housing	1.4408
Seat seal material	PTFE
Seals material	FPM PTFE
Ball material	Cast stainless steel
Material number for ball	1.4408
Shaft material	High-alloy stainless steel
Material number for shaft	1.4401
Product weight	660 g
Certification	CRN
Corrosion resistance class (CRC)	4 - Particularly high corrosion stress