

Pneumatic muffler U-PK-4

Part number: 4932

FESTO



Data sheet

Feature	Value
Type code	U
Mounting position	Any
Symbol	00991473
Operating pressure	0 bar ... 10 bar
Flow rate with respect to atmosphere	580 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Noise level	77 dB(A)
Ambient temperature	-10 °C ... 70 °C
Product weight	4.1 g
Pneumatic connection	PK-4
Cushioning insert material	Bronze
Material of screwed trunnion	Brass
Note on materials	Free of copper and PTFE RoHS-compliant