

Flange mounting DAMF-Q12-40

Part number: 4965022

FESTO



Data sheet

Feature	Value
Size	40
Type code	DAMF
Mounting position	Any
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	0 °C ... 60 °C
Max. tightening torque	12 Nm
Product weight	472 g
Type of mounting	With through-hole
Note on materials	RoHS-compliant
Mounting material	Steel, galvanized
Material of screws	Steel, galvanized