

# Quick coupling EAMD-25-22-8-10X12

Part number: 5010861

FESTO



## Data sheet

Feature	Value
Diameter of holder 1	8 mm
Diameter of holder 2	10 mm
Size	25
Nominal length	22 mm
Type code	EAMD
Mounting position	Any
Max. rotational speed	8000 1/min
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	3.2 kgmm <sup>2</sup>
Transferable torque	8 Nm
Product weight	43.4 g
Note on materials	RoHS-compliant