

# Quick coupling EAMD-30-22-16-10X12

Part number: 5030235

FESTO



## Data sheet

| Feature                | Value               |
|------------------------|---------------------|
| Diameter of holder 1   | 16 mm               |
| Diameter of holder 2   | 10 mm               |
| Size                   | 30                  |
| Nominal length         | 22 mm               |
| Type code              | EAMD                |
| Mounting position      | Any                 |
| Max. rotational speed  | 8000 1/min          |
| Storage temperature    | -25 °C ... 60 °C    |
| Relative air humidity  | 0 - 95 %            |
| Ambient temperature    | -25 °C ... 60 °C    |
| Mass moment of inertia | 4 kgmm <sup>2</sup> |
| Transferable torque    | 9 Nm                |
| Product weight         | 44.8 g              |
| Note on materials      | RoHS-compliant      |