


Quick coupling EAMD-42-40-18-16X25

Part number: 5056644

FESTO



Data sheet

Feature	Value
Diameter of holder 1	18 mm
Diameter of holder 2	16 mm
Size	42
Nominal length	40 mm
Type code	EAMD
Mounting position	Any
Max. rotational speed	6000 1/min
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	39 kgmm ²
Transferable torque	17 Nm
Product weight	192 g
Note on materials	RoHS-compliant