


# Linear actuator DLGF-KF-32-200-PPSA

Part number: 5074802

FESTO



## Data sheet

Feature	Value
Stroke	200 mm
Piston diameter	32 mm
Type code	DLGF
Cushioning	Self-adjusting pneumatic end-position cushioning
Mounting position	Any
Guide	Recirculating ball bearing guide
Driver principle	Positive locking (slot)
Position sensing	For proximity sensor
Symbol	00991254
Operating pressure	0.15 MPa ... 0.8 MPa
Operating pressure	1.5 bar ... 8 bar
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	0 °C ... 60 °C
Cushioning length	11.6 mm
Max. force F <sub>y</sub>	1300 N
Max. force F <sub>z</sub> (towards actuator)	1600 N
Max. force +F <sub>z</sub> (away from actuator)	950 N
Max. torque M <sub>x</sub>	30 Nm
Max. torque M <sub>y</sub>	50 Nm
Max. torque M <sub>z</sub>	50 Nm
Theoretical force at 6 bar, retracting	483 N
Theoretical force at 6 bar, advancing	483 N
Moving mass	1290 g
Product weight	4213 g
Alternative connections	See product drawing
Type of mounting	Direct mounting via through-hole With accessories
Pneumatic connection	G1/8
Note on materials	RoHS-compliant Copper-free
Cover material	Die-cast aluminum, coated
Seals material	NBR TPE-U(PU)

Feature	Value
Housing material	Aluminum, anodized