


Linear actuator DLGF-G-20-200-PPSA

Part number: 5074920

FESTO



Data sheet

Feature	Value
Stroke	200 mm
Piston diameter	20 mm
Type code	DLGF
Cushioning	Self-adjusting pneumatic end-position cushioning
Mounting position	Any
Guide	Basic guide
Driver principle	Positive locking (slot)
Position sensing	For proximity sensor
Symbol	00995280
Operating pressure	0.2 MPa ... 0.8 MPa
Operating pressure	2 bar ... 8 bar
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	0 °C ... 60 °C
Cushioning length	9.6 mm
Max. force F _y	0 N
Max. force F _z (towards actuator)	98 N
Max. force +F _z (away from actuator)	54 N
Max. torque M _x	0.6 Nm
Max. torque M _y	2.2 Nm
Max. torque M _z	0.7 Nm
Theoretical force at 6 bar, retracting	188 N
Theoretical force at 6 bar, advancing	188 N
Moving mass	66 g
Product weight	1153 g
Alternative connections	See product drawing
Type of mounting	Direct mounting via through-hole With accessories
Pneumatic connection	M5
Note on materials	RoHS-compliant Copper-free
Cover material	Die-cast aluminum, coated
Seals material	NBR TPE-U(PU)

Feature	Value
Housing material	Aluminum, anodized