

Clevis foot LN-100

Part number: 5152

FESTO



Data sheet

Feature	Value
Size	100
Type code	LN
Based on norm	ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290)
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-40 °C ... 150 °C
Product weight	1234 g
Note on materials	Free of copper and PTFE RoHS-compliant
Mounting material	Spherulitic graphite iron