



Motor cable NEBM-SF1W31-EH-2.6-Q15N-LE28

Part number: 5213342

FESTO



Data sheet

Feature	Value
Type code	NEBM
Conforms to standard	DIN 47100
Cable designation	Without label holder
Contact durability	30
Product weight	770 g
Electrical connection 1, function	Field device end
Electrical connection 1, design	Rectangular
Electrical connection 1, connection type	Plug
Electrical connection 1, cable outlet	Angled
Electrical connection 1, information on cable outlet	90°
Electrical connection 1, connection technology	Connection diagram F1
Electrical connection 1, number of pins/wires	31
Electrical connection 1, occupied pins/wires	31
Electrical connection 1, type of mounting	Snap-locking
Electrical connection for input 1, connection pattern	00995929
Electrical connection 2, function	Control side
Electrical connection 2, connection type	Cable
Electrical connection 2, connection technology	Open end
Electrical connection 2, number of pins/wires	28
Electrical connection 2, occupied pins/wires	28
DC operating voltage range	0 V ... 50 V
Nominal operating voltage DC	24 V
Current rating at 40°C	0.5 A
Surge resistance	0.25 kV
Cable length	2.6 m
Cable characteristic	Suitable for energy chains
Connector cable test conditions	Test conditions on request
Bending radius, fixed cable installation	≥49.5 mm
Bending radius, flexible cable installation	≥74.25 mm
Cable diameter	9.9 mm
Cable diameter tolerance	± 0.2 mm
Cable design	1 x (6 x 0.35 mm ²) + 2 x (4 x 0.15 mm ²)
Nominal conductor cross section	0.35 mm ² 0.15 mm ²
Wire ends	Cable end sleeve
Degree of protection	IP20

Feature	Value
Note on degree of protection	In mounted state
Ambient temperature	-20 °C ... 75 °C
Ambient temperature with flexible cable installation	-5 °C ... 70 °C
Storage temperature	-25 °C ... 55 °C
CE marking (see declaration of conformity)	As per EU RoHS directive
Note on materials	Contains paint-wetting impairment substances RoHS-compliant
Contamination level	1
Corrosion resistance class (CRC)	1 - Low corrosion stress
Material of cable sheath	TPE-U(PUR)
Color cable sheath	Black
Housing material	PA
Housing colour	Black
Material of pin contacts	Copper alloy, tin-plated