

Manifold
MHA3-PR4-3-1/8
Part number: 525222

FESTO



Data sheet

Feature	Value
Type code	MH3
Max. no. of valve positions	4
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Sub-base mounting type	With through-hole With H-rail
Pneumatic valve mounting type	With internal thread
Pneumatic connection 1/33	G1/4
Pneumatic connection 2	Internal thread G1/8
Pneumatic connection 3/11	G1/4
Note on materials	Free of copper and PTFE
Material of sub-base	Wrought aluminum alloy