

Plastic tubing PAN-V0-10X1,25-GN

Part number: 525472

FESTO



Data sheet

| Feature | Value |
|--|---|
| Outside diameter | 12 mm |
| Bending radius relevant for flow rate | 56 mm |
| Inside diameter | 7.5 mm |
| Min. bending radius | 34 mm |
| Type code | PAN-V0 |
| Temperature-dependent operating pressure | -0.95 bar ... 12 bar |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:-:-] Mineral oil Water as per manufacturer's declaration at www.festo.com |
| Material fire test | UL94 V-0 (casing) |
| Ambient temperature | -30 °C ... 90 °C |
| Product weight by length | 0.088 kg/m |
| Pneumatic connection | For plug connection outside diameter 10 mm |
| Color | Green |
| Shore hardness | A 72 +/-4 D 57 +/-3 |
| Note on materials | RoHS-compliant |
| Material of pneumatic tubing | PA12-P PVC-P |