

Intermediate position attachment SLG-Z-18-A

Part number: 525681

FESTO



Data sheet

Feature	Value
Type code	SLG-Z
Mounting position	Any
Structural design	Swivel module
Position sensing	For proximity sensor
Operating pressure	1 bar ... 8 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Ambient temperature	-10 °C ... 60 °C
Product weight	75 g
Type of mounting	With through-hole and dowel pin
Pneumatic connection	M3
Note on materials	Free of copper and PTFE
Stops material	Steel, nickel-plated
Seals material	PUR
Housing material	Aluminum Hard-anodized