

Plug SEA-GS-HAR-4POL

Part number: 525928

FESTO



Data sheet

Feature	Value
Type code	SEA
Based on norm	EN 61076-2-101 EN 61984
Type of mounting	With thread
Mounting position	Any
Product weight	11.5 g
Electrical connection	4-pin M12x1 Straight plug/insulation displacement connector
DC operating voltage range	≤32 V
Operating voltage range AC	≤32 V
Current rating at 40°C	4 A
Surge resistance	0.8 kV
Cable fitting	Pg9
Approved cable diameter	4 mm ... 5.1 mm
Individual wire diameter	0.1 mm
Wire diameter	1.2 mm ... 1.6 mm
Connection cross section	0.25 mm ² ... 0.5 mm ²
Degree of protection	IP67
Ambient temperature	-25 °C ... 85 °C
Note on materials	RoHS-compliant
Contamination level	3
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Housing material	Die-cast zinc Nickel-plated
Permissible insulating sheath	PVC