


Air preparation unit FRC-QS4-D-7-O-5M-MICRO

Part number: 527878

FESTO



Data sheet

Feature	Value
Size	Micro
Type code	FRC
Series	D
Actuator lock	Rotary knob with detent
Mounting position	Vertical +/- 5°
Condensate drain	Manually rotating
Structural design	Filter regulator without pressure gauge Proportional standard oil mist lubricator
Max. condensate volume	3 ml
Grade of filtration	5 µm
Symbol	00991550
Pressure gauge	M5 prepared
Operating pressure	1 bar ... 10 bar
Pressure regulation range	0.5 bar ... 7 bar
Max. pressure hysteresis	0.3 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [-:-:-]
Temperature of medium	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Product weight	139 g
Type of mounting	Line installation With accessories
Pneumatic connection 1	QS-4
Pneumatic connection 2	QS-4
Housing material	Wrought aluminum alloy
Material of bowl	PC