



Pressure regulator MS4-LRB-1/4-D6-VS-AS-Z

Part number: 529482

FESTO



Data sheet

| Feature | Value |
|--|--|
| Size | 4 |
| Type code | MS4-LRB |
| Series | MS |
| Actuator lock | Rotary knob with detent can be closed with accessories |
| Mounting position | Any |
| Structural design | Directly controlled diaphragm regulator with continuous compressed air supply |
| Controller function | Outlet pressure constant With primary pressure compensation With secondary exhausting With return flow function |
| Symbol | 00995252 |
| Operating pressure | 0.8 bar ... 14 bar |
| Pressure regulation range | 0.3 bar ... 7 bar |
| Max. pressure hysteresis | 0.25 bar |
| Standard nominal flow rate | 1700 l/min |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gas |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| Storage temperature | -10 °C ... 60 °C |
| For use in the food industry | See supplementary material information |
| Temperature of medium | -10 °C ... 60 °C |
| Ambient temperature | -10 °C ... 60 °C |
| Product weight | 222 g |
| Type of mounting | Optionally: Front panel mounting Line installation With accessories |
| Pneumatic connection 1 | G1/4 |
| Pneumatic connection 2 | G1/4 |
| Note on materials | Free of copper and PTFE RoHS-compliant |
| Material of sub-base | Die-cast aluminum |
| Material of operator panel | PA POM |

| Feature | Value |
|--------------------|-------------------|
| Seals material | NBR |
| Housing material | Die-cast aluminum |
| Diaphragm material | NBR |