

Quick coupling EAMC-B-15-22-5-5

Part number: 530085

FESTO



Data sheet

Feature	Value
Diameter of holder 1	5 mm
Diameter of holder 2	5 mm
Size	15
Nominal length	22 mm
Type code	EAMC
Mounting position	Any
Max. rotational speed	12000 1/min
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	0.13 kgmm ²
Transferable torque	1 Nm
Product weight	6 g
Note on materials	RoHS-compliant