

Quick coupling socket KD4-1/4-I

Part number: 531636

FESTO



Data sheet

Feature	Value
Nominal width	7.2 mm
Type code	KD4
Operating pressure for entire temperature range	-0.95 bar ... 12 bar
Standard nominal flow rate	1130 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-10 °C ... 60 °C
Nominal tightening torque	9.5 Nm
Tolerance for nominal tightening torque	± 15%
Product weight	88 g
Pneumatic connection 1	Internal thread G1/4
Note on materials	RoHS-compliant