

Quick coupling socket KD4-CK-6

Part number: 531639

FESTO



Data sheet

Feature	Value
Nominal width	4.9 mm
Type code	KD4
Operating pressure for entire temperature range	-0.95 bar ... 12 bar
Standard nominal flow rate	432 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-10 °C ... 60 °C
Product weight	63 g
Pneumatic connection 1	CK-6
Note on materials	RoHS-compliant