

Quick coupling socket KD3-1/8-A-R

Part number: 531659

FESTO



Data sheet

| Feature | Value |
|---|---|
| Nominal width | 5 mm |
| Type code | KD3 |
| Operating pressure for entire temperature range | -0.95 bar ... 12 bar |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:-:-] |
| Information on operating and pilot media | Operation with oil lubrication possible |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| Ambient temperature | -10 °C ... 60 °C |
| Nominal tightening torque | 5 Nm |
| Tolerance for nominal tightening torque | ± 15% |
| Product weight | 28 g |
| Pneumatic connection 1 | External thread G1/8 |
| Note on materials | RoHS-compliant |