

# Quick coupling plug KS4-1/4-I

Part number: 531678

FESTO



## Data sheet

| Feature   | Value   |
|---|---|
| Nominal width                                   | 7.85 mm                                       |
| Type code                                       | KS4   |
| Operating pressure for entire temperature range | -0.95 bar ... 12 bar                          |
| Standard nominal flow rate                      | 1130 l/min                                    |
| Operating medium                                | Compressed air as per ISO 8573-1:2010 [7:-:-] |
| Information on operating and pilot media        | Operation with oil lubrication possible       |
| Corrosion resistance class (CRC)                | 1 - Low corrosion stress                      |
| Ambient temperature                             | -10 °C ... 60 °C                              |
| Nominal tightening torque                       | 9.5 Nm  |
| Tolerance for nominal tightening torque         | ± 15%   |
| Product weight                                  | 31 g  |
| Pneumatic connection 1                          | Internal thread G1/4                          |
| Note on materials                               | RoHS-compliant                                |