


# Vacuum generator VN-07-N-I3-PQ2-VQ2-A

Part number: 532635

FESTO



## Data sheet

Feature	Value
Nominal width of Laval nozzle	0.7 mm
Width dimension	14.5 mm
Type code	VN
Mounting position	Any
Ejector characteristics	Inline High suction volume
Integrated function	Ejector pulse valve, pneumatic
Structural design	Straight design
Symbol	00991484
Operating pressure for max. suction rate	4 bar
Operating pressure	1 bar ... 8 bar
Nominal operating pressure	6 bar
Max. suction rate with respect to atmosphere	32.6 l/min
Air supply time at nominal operating pressure	0.89 s
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication not possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
Temperature of medium	0 °C ... 60 °C
Cleaning advice	Soap suds
Noise level at nominal operating pressure	78 dB(A)
Ambient temperature	0 °C ... 60 °C
Product weight	41 g
Type of mounting	Line installation
Pneumatic connection 1	QS-6
Vacuum connection	QS-6
Material of connecting thread	Wrought aluminum alloy, anodized
Note on materials	Free of copper and PTFE RoHS-compliant
Seals material	NBR
Female nozzle material	POM
Housing material	PA-reinforced POM-reinforced
Material of screws	Steel
Material of jet nozzle	Wrought aluminum alloy

Feature	Value
Material of pneumatic fitting	Brass Nickel-plated