

Push-in T-fitting QBT-M5-3/16-U-M

Part number: 533249

FESTO



Data sheet

| Feature | Value |
|-------------------------------------------------|-----------------------------------------------|
| Size | Standard |
| Nominal width | 2.997 mm |
| Type code | QBT |
| Type of seal on screwed trunnion | Sealing ring |
| Operating pressure for entire temperature range | -0.951 bar ... 9.997 bar |
| Maritime classification | See certificate |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:-:-] |
| Information on operating and pilot media | Operation with oil lubrication possible |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| Ambient temperature | 0 °C ... 60 °C |
| Nominal tightening torque | 0.5 Nm |
| Tolerance for nominal tightening torque | ± 10% |
| Product weight | 11.907 g |
| Releasing ring color | Gray |
| Note on materials | RoHS-compliant |
| Housing material | PBT |
| Material of threaded seal | NBR |
| Releasing ring material | POM |
| Material of tube retaining claw | High-alloy stainless steel |