



Transmitter SOEG-S-M18W-K-L

Part number: 537693

FESTO



Data sheet

Feature	Value
Type code	SOEG
Design	Round
Conforms to standard	EN 60947-5-2
Symbol	00991642
Certification	RCM compliance mark c UL us - Listed (OL)
CE marking (see declaration of conformity)	As per EU EMC directive
Note on materials	Free of copper and PTFE
Measured variable	Position
Measuring principle	Optoelectronic
Method of measurement	Through-beam sensor Transmitter
Type of light	Red
Working range	20000 mm
Ambient temperature	-25 °C ... 55 °C
Voltage drop	≤2 V
Short-circuit protection	Pulsed
DC operating voltage range	10 V ... 36 V
Residual ripple	20 %
Idle current	15 mA
Reverse polarity protection	for all electrical connections
Electrical connection	3-wire Cable
Cable length	2.5 m
Material of cable sheath	TPE-U(PUR)
Size	M18x1
Type of mounting	With lock nut
Tightening torque	20 Nm
Product weight	124 g
Housing material	Brass Chrome-plated
Material of union nut	Brass Chrome-plated
Ambient temperature with flexible cable installation	-5 °C ... 55 °C
Degree of protection	IP65 IP67
Corrosion resistance class (CRC)	1 - Low corrosion stress