

Pneumatic muffler UOM-3/8

Part number: 538433

FESTO



Data sheet

Feature	Value
Type code	UOM
Type of seal on screwed trunnion	without seal
Mounting position	Any
Structural design	Pneumatic muffler, open
Symbol	00991473
Operating pressure of vacuum generator	0 bar ... 8 bar
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Ambient temperature	0 °C ... 60 °C
Type of mounting	Screw-in
Product weight	22.7 g
Pneumatic connection	G3/8
Cushioning insert material	PU foam
Material of screwed trunnion	POM
Note on materials	Free of copper and PTFE
Housing material	POM
Interior tube material	Wrought aluminum alloy