

# Muffler extension UOMS-3/8

Part number: 538437

FESTO



## Data sheet

Feature	Value
Type code	UOMS
Type of seal on screwed trunnion	without seal
Mounting position	Any
Structural design	Pneumatic muffler, open
Symbol	00991473
Operating pressure of vacuum generator	0 bar ... 8 bar
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Ambient temperature	0 °C ... 60 °C
Type of mounting	Engaging
Product weight	17.5 g
Cushioning insert material	PU foam
Material of screwed trunnion	POM
Note on materials	Free of copper and PTFE
Housing material	POM
Interior tube material	Wrought aluminum alloy