

Stroke reduction HGPL-HR-14

Part number: 539092

FESTO



Data sheet

Feature	Value
Size	14
Adjustable end position range/length	40 mm
Type code	HGPL
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Ambient temperature	5 °C ... 60 °C
Product weight	45 g
Type of mounting	Screwed on to pneumatic gripper
Note on materials	Free of copper and PTFE RoHS-compliant
Plate material	Wrought aluminum alloy