

90°-connection plate VABF-S4-1-A2G2-G14

Part number: 539721

FESTO



Data sheet

Feature	Value
Width	26 mm
Type code	VABF
Based on norm	ISO 15407-2
Mounting position	Any
Operating pressure	-0.09 MPa ... 1 MPa
Operating pressure	-0.9 bar ... 10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	0 - No corrosion stress
Degree of protection	IP65 NEMA 4
Ambient temperature	-5 °C ... 50 °C
Product weight	217 g
Type of mounting	With through-hole
Housing material	Die-cast aluminum