

# Parallel kit EAMM-U-D40-55A

Part number: 543157

FESTO



## Data sheet

Feature	Value
Size	40
Type code	EAMM-U
Mounting position	Any
Max. rotational speed	5000 1/min
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	0 °C ... 50 °C
Mass moment of inertia	10.016 kgmm <sup>2</sup>
No-load driving torque	0.1 Nm
Transferable torque	3 Nm
Product weight	530 g
Note on materials	Contains paint-wetting impairment substances