

Electronics module VMPA2-FB-EMS-D2-4

Part number: 543332

FESTO



Data sheet

Feature	Value
Type code	VMPA2
Diagnostics	Condition monitoring Wire break per valve coil Short circuit of pneumatic valves Undervoltage of pneumatic valves
Max. no. of valve positions	2
Max. no. of solenoid coils	4
Intrinsic current consumption at load voltage	3 mA
Intrinsic current consumption at operating voltage	8 mA
Nominal pick-up current per solenoid coil	99 mA to 24 ms
Nominal current with current reduction	18 mA after 24 ms
Corrosion resistance class (CRC)	1 - Low corrosion stress (when installed)
Product weight	20 g
Housing material	POM
Note on materials	RoHS-compliant