

Electronics module VMPA1-FB-EMG-D2-8

Part number: 543333

FESTO



Data sheet

Feature	Value
Type code	VMPA1
Diagnostics	Condition monitoring Wire break per valve coil Short circuit of pneumatic valves Undervoltage of pneumatic valves
Max. no. of valve positions	4
Max. no. of solenoid coils	8
Intrinsic current consumption at load voltage	23 mA
Intrinsic current consumption at operating voltage	8 mA
Nominal pick-up current per solenoid coil	58 mA to 24 ms
Nominal current with current reduction	9 mA after 24 ms
Corrosion resistance class (CRC)	1 - Low corrosion stress (when installed)
Product weight	20 g
Housing material	POM
Note on materials	RoHS-compliant