

# Multi-pin node VABE-S6-1LF-C-M1-C36M

Part number: 543412

FESTO



## Data sheet

Feature	Value
Type code	VABE
Based on norm	EN 61984
Mounting position	Any
Max. no. of valve positions	16 for bistable pneumatic valves 32 for monostable pneumatic valves
Max. residual current	6 A
Nominal operating voltage AC	110 V
Nominal operating voltage DC	24 V
Surge resistance	1.5 kV
Current rating at 40°C	1 A
Contamination level	3
Permissible voltage fluctuations	+/- 10 %
CE marking (see declaration of conformity)	As per EU low voltage directive
Corrosion resistance class (CRC)	0 - No corrosion stress
Degree of protection	IP65 NEMA 4
Ambient temperature	-5 °C ... 50 °C
Product weight	545 g
Electrical actuation	Multi-pin
Electrical connection	Socket/terminal strip
Cover material	PA
Housing material	Die-cast aluminum