

Quick coupling EAMC-30-32-8-9

Part number: 543423

FESTO



Data sheet

Feature	Value
Diameter of holder 1	8 mm
Diameter of holder 2	9 mm
Size	30
Nominal length	32 mm
Type code	EAMC
Mounting position	Any
Max. rotational speed	8000 1/min
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	5.87 kgmm ²
Transferable torque	12.5 Nm
Product weight	48 g
Note on materials	RoHS-compliant