

Branching module MS6-A-RMV-IPM-80

Part number: 543501

FESTO



Data sheet

Feature	Value
Type code	MS6-A-RMV
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Temperature of medium	-10 °C ... 60 °C
Product weight	236 g
Note on materials	RoHS-compliant
Material of sub-base	Die-cast aluminum
Seals material	NBR
Hollow bolt material	Die-cast aluminum
Module connector material	Die-cast aluminum
Material of screws	Steel