


Signal conditioner SVE4-IS-R-HM8-2N-M8

Part number: 544221

FESTO



Data sheet

Feature	Value
Type code	SVE4
Symbol	00991963
Certification	RCM compliance mark c UL us - Listed (OL)
UL-ambient temperature	-20 °C ... 60 °C
CE marking (see declaration of conformity)	As per EU EMC directive
Note on materials	Free of copper and PTFE
Signal range	0 - 20 mA +/- 0.6 mA
Ambient temperature	-20 °C ... 70 °C
Switching output	2xNPN
Switching function	Freely programmable
Switching element function	Switchable
Short-circuit protection	Pulsed
Overload protection	Available
DC operating voltage range	10 V ... 30 V
Electrical connection, input	Socket M8x1 4-pin as per EN 60947-5-2
Electrical connection, output	Plug M8x1 4-pin as per EN 60947-5-2
Product weight	19 g
Housing material	ABS
Setting options	Teach-in
Degree of protection	IP65
Corrosion resistance class (CRC)	2 - Moderate corrosion stress