


Vertical pressure supply plate VABF-S2-1-P1A3-N38

FESTO

Part number: 546094



Data sheet

| Feature | Value |
|--|--|
| Width | 43 mm |
| Type code | VABF |
| Based on norm | ISO 5599-2 |
| Mounting position | Any |
| Pneumatic vertical stacking | Alternative pressure supply for 1 |
| Symbol | 00991883 |
| Operating pressure | -0.09 MPa ... 1 MPa |
| Operating pressure | -0.9 bar ... 10 bar |
| Standard nominal flow rate | 1300 l/min |
| CE marking (see declaration of conformity) | As per EU low voltage directive |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 0 - No corrosion stress |
| Degree of protection | IP65 NEMA 4 |
| Ambient temperature | -5 °C ... 50 °C |
| Product weight | 340 g |
| Vertical stacking mounting type | On manifold sub-base On individual sub-base |
| Note on materials | RoHS-compliant |
| Housing material | Die-cast aluminum |