

Adapter AD-G1-1NPT-I

Part number: 546546

FESTO



Data sheet

Feature	Value
Nominal width	21.4 mm
Type code	AD
Operating pressure for entire temperature range	-0.95 bar ... 10 bar
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-10 °C ... 60 °C
Max. tightening torque, pneumatic connection 1	90 Nm
Max. tightening torque, pneumatic connection 2	35 Nm
Product weight	212.68 g
Pneumatic connection 1	G1
Pneumatic connection 2	1 NPT
Note on materials	RoHS-compliant