


Vacuum generator cartridge VN-07-L

FESTO

Part number: 547696



Data sheet

Feature	Value
Nominal width of Laval nozzle	0.7 mm
Type code	VN
Mounting position	Any
Ejector characteristics	Standard High suction volume
Symbol	00991490
Operating pressure	1 bar ... 8 bar
Nominal operating pressure	6 bar
Max. suction rate with respect to atmosphere	30.9 l/min
Air supply time at nominal operating pressure	0.82 s
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication not possible
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Temperature of medium	0 °C ... 60 °C
Ambient temperature	0 °C ... 60 °C
Product weight	1.65 g
Seals material	NBR
Female nozzle material	POM
Material of jet nozzle	Wrought aluminum alloy