

# Cover VAEM-S6-C-S10-R5

Part number: 549049

FESTO



## Data sheet

Feature	Value
Type code	VAEM
Max. no. of valve positions	10 for bistable pneumatic valves 20 for monostable pneumatic valves
Max. residual current	10 A
Nominal operating voltage DC	24 V
Permissible voltage fluctuations	+/- 10 %
Corrosion resistance class (CRC)	0 - No corrosion stress
Degree of protection	IP65 NEMA 4
Ambient temperature	-5 °C ... 50 °C
Product weight	230 g
Number of electrical connections	10
Electrical connection	5-pin M12 Plug
Housing material	PA