

# Connection block CPE14-3/2-PRS-3/8-4

Part number: 550561

**FESTO**



## Data sheet

| Feature                                   | Value                         |
|-------------------------------------------|-------------------------------|
| Width dimension                           | 20 mm                         |
| Type code                                 | CPE14-PRS                     |
| Mounting position                         | Any                           |
| Max. no. of valve positions               | 4                             |
| Max. no. of pressure zones                | 2                             |
| Burst pressure                            | 5 MPa                         |
| Burst pressure                            | 50 bar                        |
| Burst pressure                            | 725 psi                       |
| Operating pressure                        | -0.09 MPa ... 1 MPa           |
| Operating pressure                        | -0.9 bar ... 10 bar           |
| Corrosion resistance class (CRC)          | 2 - Moderate corrosion stress |
| Temperature of medium                     | -5 °C ... 50 °C               |
| Ambient temperature                       | -5 °C ... 50 °C               |
| Max. tightening torque for valve mounting | 1.2 Nm                        |
| Product weight                            | 280 g                         |
| Manifold block type of mounting           | With through-hole             |
| Pneumatic valve mounting type             | With internal thread          |
| Pneumatic connection 1                    | G3/8                          |
| Pneumatic connection 3                    | G3/8                          |
| Pneumatic connection 5                    | G3/8                          |
| Note on materials                         | RoHS-compliant                |
| Manifold rail material                    | Wrought aluminum alloy        |