


Axial kit EAMM-A-D60-100A

Part number: 550983

FESTO



Data sheet

Feature	Value
Type code	EAMM-A
Mounting position	Any
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C ... 60 °C
Transferable torque	17 Nm
Product weight	1170 g
Interface code, actuator	D60A D60B D60C
Interface code, motor in	100A
Note on materials	Contains paint-wetting impairment substances RoHS-compliant